


Expertise Applied | Answers Delivered




EV Charging Infrastructure

Supercharged Solutions to Enhance Safety, Efficiency, and Reliability

Types of Electric Vehicle Charging Stations


As defined by SAE J1772
 As defined by IEC 61851-1




* Charge time dependent on vehicle's battery capacity and charge acceptance rate

Littelfuse, Inc. © 2019 2

Global Electric Vehicle Charging Equipment Market





Source: Navigant Research - Market Data: Electric Vehicle Charging Equipment, 2017

Market Trends and Drivers

Increasing production of electrified vehicles: estimated 6 million vehicles in 2019 growing to 16 million vehicles in 2023

Limited charging infrastructure in most regions

Production of new EV charging equipment to increase at a compound annual growth rate (CAGR) of 22% between 2018 and 2026

Majority of charging to occur at home or workplace during a span of several hours (AC charging)

Consumer demand for charging times to emulate fuel refill time for long-distance trips (DC charging)

Increasing voltage and power output of DC chargers for fast charging

Evolving business models: increase property value; revenue generation

Sources: Boston Consulting Group – The Electric Car Tipping Point, 2018; Navigant Research – Market Data: Electric Vehicle Charging Equipment, 2017; Littelfuse estimates



AC Charging Station

Service Access Panel:

Reed or Hall Effect Security Sensor

AC Input:


- Power Fuse Overcurrent Protection
- Fuse Block Mounting Accessory

Auxiliary Power Supply:


- Cartridge Fuse Overcurrent Protection
- TMOV/MOV, GDT Surge Protection
- SMPS^{*} Buck/Boost Module
- SMPS^{*} Opto-isolator Feedback Control
- SMPS^{*} Diode/Rectifier
- TVS Diode Overvoltage Protection
- PPTC Resettable Overcurrent Protection
- NTC Thermistor Temperature Sensing

* Switched-mode Power Supply





AC Charger Functional Block Diagram




 Power
 Data/Signal

🛃 Lit	telfuse
Expertise Applied	Answers Delivered

Technology	Product Series
AC Fuse	JLLS, JLLN, KLKD
Fuse Block/Holder	LFT, LPSM
AC Fuse (PCB level)	314, 324, 215, NANO ^{2®}
Metal-Oxide Varistor	AUMOV, TMOV, UltraMOV
Gas Discharge Tube	CG2, CG3
TVS Diode	AK3, AK6, AK10, LTKAK6, LTKAK10
SIDACtor [®] Protection Thyristor	Pxxx0ME, Pxxx0FNL
Silicon-Controlled Rectifier (active rectification)	SJ
Diode (passive rectification)	DPG, VBExx, DST, DSA, DSB
TVS Diode	P6SMB, SMBJ
Resettable PPTC	miniSMD
MOSFET	Polar [™] Power, CPC37xx
Optical Isolator	LOC11x, LIA1xx
	AC Fuse Fuse Block/Holder AC Fuse (PCB level) Metal-Oxide Varistor Gas Discharge Tube TVS Diode SIDACtor® Protection Thyristor Silicon-Controlled Rectifier (active rectification) Diode (passive rectification) TVS Diode Resettable PPTC MOSFET

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.

AC Charger Functional Block Diagram



Legend: Power Data/Signal



	Technology	Product Series	
3	NFC Analog Front-End	NCD1300	
	Diode Array	AQ24CAN, SM24CANx	
4	TVS Diode	SMF, SMAJ, SAC	
	Diode Array Polymer ESD	SEP0xx, SP402x XGD	
5	Magnetic Sensor	59060, 59135, 55075, 55100	
6	Temperature Sensor	setP™, PPG, USW, Glass Coated Thermistor	

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.

DC Charging Station

Service Access Panel:

Reed or Hall Effect Security Sensor

User Interface:

- TVS Diode Overvoltage Protection
- Diode Array/Polymer ESD Suppressor


Communications:

- NFC Analog Front-End
- Diode Array/Polymer ESD Suppressor

Power Module:



- Cartridge Fuse Overcurrent Protection
- TMOV/MOV, GDT, TVS Diode, SIDACtor Surge Protection
- Rectifier Module Power Conversion
- IGBT Power Conversion
- Si or SiC MOSFET Power Conversion
- Gate Driver Control
- Si or SiC Diode Power Conversion
- NTC Thermistor Temperature Sensor



Electrical Distribution:

- Power Fuse Overcurrent Protection
- Fuse Block Mounting Accessory
- Earth-Fault Protection Relay
- Current Transformer Leakage
 Current Sensing

Auxiliary Power Supply:

- Cartridge Fuse Overcurrent Protection
- TMOV/MOV, GDT Surge Protection
- SMPS^{*} Buck/Boost Module
- SMPS^{*} Opto-isolator Feedback Control
- SMPS^{*} Diode/Rectifier
- TVS Diode Overvoltage Protection
- PPTC Resettable Overcurrent Protection
- NTC Thermistor Temperature Sensing

Charging Plug:


 NTC Thermistor or RTD Temperature Sensing

* Switched-mode Power Supply

Expertise Applied Answers Delivered

ittelfuse

DC Charger Functional Block Diagram




	Technology	Product Series
	AC Fuse (cabinet level)	JLS JLLS, LDC
	AC Fuse (PCB level)	606, 504, 505, 314, 215, NANO ^{2®}
	Gas Discharge Tube	CG2, CG3
1	Metal-Oxide Varistor	AUMOV, TMOV, UltraMOV
	TVS Diode	AK3, AK6, AK10, LTKAK6, LTKAK10
	SIDACtor [®] Protection Thyristor	Pxxx0ME, Pxxx0FNL
	Current Transformer	SE-CS30
2	AC Earth-Fault Relay	SE-704
	Silicon-Controlled Rectifier	SJ //
	MOSFET	X and X2-Class Ultra Junction FETs
3	Optical Isolator	LOC11x, LIA1xx
	TVS Diode	P6SMB
	Resettable PPTC	miniSMD

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.

Expertise Applied Answers Delivered

DC Charger Functional Block Diagram




	Technology	Product Series
	Bridge Rectifier	DMA200X1600NA, MDNA240U2200ED
	SiC or Si MOSFET	LSIC1MO, X2-Class Ultra Junction
	IGBT	XPT™, MIXA, MIXG
4	TVS Diode	TPSMx
	Diode	LSIC2SD, SONIC-FRD™, FRED DSE
	Temperature Sensor	setP [™] , USUR1000, Epoxy Coated Thermistor
	High-Speed DC Fuse	L50QS, L70QS, L75QS, PSR
5	Gate Driver	IXDN604, IX4340N, IX332B
	SiC or Si MOSFET	LSIC1MO, MCB60P1200TLB, X2-Class Ultra Junction
	TVS Diode	TPSMx
6	Diode	LSIC2SD, DCG SiC Diode Module, HiPerFRED™
	Temperature Sensor	setP [™] , USUR1000, Epoxy Coated Thermistor
7	Gate Driver	IXDN609, IX2113, IX332B

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.

Expertise Applied Answers Delivered

DC Charger Functional Block Diagram



	Technology	Product Series
8	DC Fuse	L50QS, L70QS, L75QS, PSR, 505, 525
ð	Output "ORing" Diode	LSIC2SD, SONIC-FRD [™] , FRED DSE
9	DC Earth-Fault Relay	SE-601
	Earth Reference Module	SE-GRM
10	Temperature Sensor	setP [™] , PPG, USW, Glass Coated Thermistor
11	NFC Analog Front-End	NCD1300
	Diode Array	AQ24CAN, SM24CANx
12	TVS Diode	SMF, SMAJ, SAC
	Diode Array Polymer ESD	SEP0xx, SP402x XGD
13	Magnetic Sensor	59060, 59135, 55075, 55100

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.



Wireless Charging System

Power Module:

- Cartridge Fuse Overcurrent Protection
- TMOV/MOV, GDT, TVS Diode, SIDACtor Surge Protection
- Rectifier Module Power Conversion
- IGBT Power Conversion
- Si or SiC MOSFET Power Conversion
- Gate Driver Control

Expertise Applied Answers Delivered

- Si or SiC Diode Power Conversion
- NTC Thermistor Temperature Sensor

Service Access Panel:

Protect

Control

Sense

• Reed and Hall Effect Security Sensor

Auxiliary Power Supply:


- Cartridge Fuse Overcurrent Protection
- TMOV/MOV, GDT Surge Protection
- SMPS^{*} Buck/Boost Module
- SMPS^{*} Opto-isolator Feedback Control
- SMPS^{*} Diode/Rectifier
- TVS Diode Overvoltage Protection
- PPTC Resettable Overcurrent
 Protection
- NTC Thermistor Temperature Sensing

Electrical Distribution:

- Power Fuse Overcurrent Protection
- Fuse Block Mounting Accessory
- Earth-Fault Protection Relay
- Current Transformer Leakage Current Sensing

* Switched-mode Power Supply

Wireless Charger Functional Block Diagram




	Technology	Product Series
	recimology	r roudet beries
	AC Fuse (cabinet level)	JLS JLLS, LDC
	AC Fuse (PCB level)	606, 504, 505, 314, 215, NANO ^{2®}
	Gas Discharge Tube	CG2, CG3
1	Metal-Oxide Varistor	AUMOV, TMOV, UltraMOV
	TVS Diode	AK3, AK6, AK10, LTKAK6, LTKAK10
	SIDACtor [®] Protection Thyristor	Pxxx0ME, Pxxx0FNL
2	Current Transformer	SE-CS30
2	AC Earth-Fault Relay	SE-704
	Silicon-Controlled Rectifier	SJ
	MOSFET	X & X2-Class Ultra Junction FETs
3	Optical Isolator	LOC11x, LIA1xx
	TVS Diode	P6SMB
	Resettable PPTC	miniSMD
Note:	Other Littelfuse solutions i	nav be suitable depending

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.

Expertise Applied Answers Delivered


Wireless Charger Functional Block Diagram



	Technology	Product Series
	TVS Diode	TPSMx
	Bridge Rectifier	DMA200X1600NA, MDNA240U2200ED
	SiC or Si MOSFET	LSIC1MO, X2-Class Ultra Junction
4	IGBT	XPT™, MIXA, MIXG
	Diode	LSIC2SD, SONIC-FRD™, FRED DSE
	Temperature Sensor	setP [™] , USUR1000, Epoxy Coated Thermistor
	High-Speed DC Fuse	L50QS, L70QS, L75QS, PSR
5	Gate Driver	IXDN604, IX4340N, IX332B
	SiC or Si MOSFET	LSIC1MO, MCB60P1200TLB, X2-Class Ultra Junction
6	TVS Diode	TPSMx
	Temperature Sensor	setP™, USUR1000, Epoxy Coated Thermistor
7	Gate Driver	IXDN609, IX2113, IX332E
	Other Littelfuse solutions i on design-specific require	may be suitable depending



Wireless Charger Functional Block Diagram



Expertise Applied Answers Delivered

	Technology	Product Series
8	Temperature Sensor	setP [™] , PPG, USW, Glass Coated Thermistor
9	Magnetic Sensor	59060, 59135, 55075, 55100
10	Diode Array (Wired CAN)	AQ24CAN, SM24CANx
10	Diode Array Polymer ESD (Wireless)	SEP0xx, SP402x XGD

Note: Other Littelfuse solutions may be suitable depending on design-specific requirements.


Select Standards for EV Charging Equipment

Standard	Title	General Scope	Region
IEC 61851 Series	Electric Vehicle Conductive Charging System	Various parts of this standard cover general requirements, along with AC chargers and DC chargers specifically.	Global
IEC 62196 Series	Plugs, Socket-Outlets, Vehicle Connectors and Vehicle Inlets - Conductive Charging of Electric Vehicles	Standards for charging plugs, sockets, and connectors.	Global
IEC 61980 Series	Electric Vehicle Wireless Power Transfer (WPT) Systems	Various parts of this standard cover general requirements for wireless charging systems, along with specific technology-based requirements.	Global
GB/T 18487 Series	Electric Vehicle Conductive Charging System	Various parts of this standard cover general requirements, along with AC chargers and DC chargers specifically.	China
GB/T 20234 Series	Connection Set for Conductive Charging of Electric Vehicles	Standards for charging plugs in China.	China
JIS TS D 0007	Basic Function of Quick Charger for the Electric Vehicle	Standard for CHAdeMO (DC) chargers in Japan.	Japan
SAE J1772*	Electric Vehicle and Plug-in Hybrid Electric Vehicle Conductive Charge Coupler	Physical, electrical, functional and performance standard for charging plugs in North America.	North America
SAE J2954*	Wireless Power Transfer for Light-Duty Plug-In/Electric Vehicles and Alignment Methodology	Interoperability, electromagnetic compatibility, EMF, minimum performance, safety and testing for wireless chargers in North America.	North America
UL 2594	Standard for Electric Vehicle Supply Equipment	Safety standard for AC chargers in North America. Tri-national standard for U.S., Canada, and Mexico (known as CAN/CSA C22.2 No. 280 in Canada and NMX-J-677-ANCE in Mexico).	North America
UL 2202	Standard for Electric Vehicle (EV) Charging System Equipment	Safety standard for DC chargers in the United States.	U.S.

* J1772TM and J2954TM are registered trademarks of SAE International



EV Charging – Technology for a Sustainable World



Littelfuse Enables Enhanced Safety, Efficiency, and Reliability for Electric Vehicle Charging

- Reference solutions to help meet global safety requirements
- System-level design compliance support
- Components designed to help meet energy efficiency
- High-volume manufacturing with highest quality standards

Global delivery network with localized distribution and customer support







Expertise Applied | Answers Delivered

A Littelfuse Technology

Littelfuse.com